

# Product data sheet

## Characteristics

# 1.5S51F

## TRANSFORMER DRY 1PH 1.5KVA

### 600V-120/240V

Product availability : Stock - Normally stocked in distribution facility



Price\* : 758.00 USD



### Main

Product or component type	Dry Sealed Transformer
Primary Voltage	600 V
Secondary Voltage	120/240 V
Full Capacity Taps	0

### Complementary

Enclosure Code	8A
Phase	1 phase
Primary to Secondary Voltage	600 V : 120/240 V
Power Rating	1.5 kVA
Temperature rise	115 °C
Height	8.25 in
Width	8.68 in
Depth	6.56 in
Enclosure mounting	Wall mounted
Enclosure material	Painted sheet steel

### Environment

Enclosure Type	NEMA 3R
Insulation temperature	356 °F (180 °C)
Product certifications	CSA cULus UL listed

### Ordering and shipping details

Category	16277 - RESIN LVGP XFMR
----------	-------------------------

Discount Schedule	PE2
GTIN	00785901020363
Nbr. of units in pkg.	1
Package weight(Lbs)	30.100000000000001
Returnability	Y
Country of origin	US

**Offer Sustainability**

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

**Contractual warranty**

Warranty period	18 months
-----------------	-----------