

# Product data sheet

## Characteristics

# 100SV51A

## TRANSFORMER DRY 1PH .1KVA

### 600V-120/240V

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 214.00 USD



### Main

Product or component type	Dry Sealed Transformer
Primary Voltage	600 V
Secondary Voltage	120/240 V
Full Capacity Taps	0

### Complementary

Enclosure Code	2A
Phase	1 phase
Primary to Secondary Voltage	600 V : 120/240 V
Power Rating	0.1 kVA
Temperature rise	55 °C
Height	5.5 in
Width	4.47 in
Depth	3.44 in
Enclosure mounting	Wall mounted
Enclosure material	Painted sheet steel

### Environment

Enclosure Type	NEMA 3R
Insulation temperature	221 °F (105 °C)
Product certifications	CSA cULus UL listed

### Ordering and shipping details

Category	16277 - RESIN LVGP XFMR
----------	-------------------------

Discount Schedule	PE2
GTIN	00785901020295
Nbr. of units in pkg.	1
Package weight(Lbs)	4.5
Returnability	N
Country of origin	US

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------