

Product data sheet

Characteristics

10172

Multi 9 - comb busbar - 2L - 18 mm pitch - 12 modules - 100A

Product availability : Non-Stock - Not normally stocked in distribution facility

Price* : 356.20 USD

10172 has not been replaced. Please contact your customer care center for more information.



! Discontinued

Main

Range	Multi 9
Product or component type	Comb busbar
Accessory / separate part category	Connection accessory
Lines description	2L
Length in 18 mm modules	12

Complementary

Number of ways	6 ways 2 L
Poles configuration for 1 way	1 x 2P
Connection pitch	18 mm
Connector type	Tooth
Distance between way	36 mm
Insulation	Insulated
Device presentation	Uncuttable
[Ie] rated operational current	100 A (40 °C)
System Voltage	240 V AC 50/60 Hz
[Ui] rated insulation voltage	1000 V AC 50/60 Hz conforming to UL 508
[Uimp] rated impulse withstand voltage	12 kV conforming to UL 508
Mounting mode	Horizontal
Mounting location	Top on tunnel type terminals
9 mm pitches	24
Width	8.5 in (216 mm)
Colour	White (RAL 9001)
Range compatibility	Multi 9 C60 / C60 UL489

Environment

Standards	UL 508
Fire resistance	1760 °F (960 °C) (30 s) conforming to UL 508

Ordering and shipping details

Category	00908 - C60N SUPPLEMENTARY PROTECTORS
Discount Schedule	DE2
GTIN	003606480385872
Nbr. of units in pkg.	1
Package weight(Lbs)	0.17000000000000001
Returnability	N
Country of origin	DE

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1336 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------