

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 7,294.00 USD



Main

Device application	Coronary/intensive care
--------------------	-------------------------

Complementary

[In] rated current	8 QO220 2P 20 A secondary circuit 45 A primary circuit
Device composition	IC29510 trim panel
Device mounting	53029BB flush mounting box 53037BB surface mounting box
Mounting support	Wall
Network number of phases	1 phase
Primary voltage	277 V
Rated power in VA	10 kVA
Secondary voltage	120 V
Supply	10XR41 via mains transformer to be ordered separately

Environment

Product certifications	UL listed
------------------------	-----------

Ordering and shipping details

Category	16003 - ICU/CCU PANELS NON STOCK
Discount Schedule	O1
Nbr. of units in pkg.	1
Package weight(Lbs)	50
Returnability	N
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel (Metallic), which is known to the State of California to cause cancer, and
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------