

# Product data sheet

## Characteristics

# 10H5S51DDI

## PANEL OPERATING ROOM ISOLATION 1PH 10KVA

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 6,050.00 USD



### Main

Device application	Operating room Coronary/intensive care
--------------------	---

### Complementary

[In] rated current	8 QO220 2P 20 A secondary circuit 30 A primary circuit
Device composition	XR29420 trim panel
Device mounting	53015BB flush mounting box 53019BB surface mounting box
Mounting support	Wall
Network number of phases	1 phase
Output voltage	120 V
Primary voltage	480 V
Rated power in VA	10 kVA
Secondary voltage	120 V
Supply	10XR51 via mains transformer to be ordered separately

### Environment

Product certifications	UL listed
------------------------	-----------

### Ordering and shipping details

Category	16001 - O.R. PANELS NON STOCK
Discount Schedule	O1
GTIN	00785901163855
Nbr. of units in pkg.	1
Package weight(Lbs)	50

Returnability	N
Country of origin	US

**Offer Sustainability**

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel (Metallic), which is known to the State of California to cause cancer, and
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

**Contractual warranty**

Warranty period	18 months
-----------------	-----------