

Product data sheet

Characteristics

10S1F

TRANSFORMER DRY 10KVA

240X480V-120/240V

Product availability : Stock - Normally stocked in distribution facility



Price* : 2,712.00 USD



Main

| | |
|---------------------------|------------------------|
| Product or component type | Dry Sealed Transformer |
| Primary Voltage | 240 x 480 V |
| Secondary Voltage | 120/240 V |
| Full Capacity Taps | 0 |

Complementary

| | |
|------------------------------|-------------------------|
| Enclosure Code | 13B |
| Phase | 1 phase |
| Primary to Secondary Voltage | 240 x 480 V : 120/240 V |
| Power Rating | 10 kVA |
| Temperature rise | 115 °C |
| Height | 14.75 in |
| Width | 9.75 in |
| Depth | 11.75 in |
| Enclosure mounting | Wall mounted |
| Enclosure material | Painted sheet steel |

Environment

| | |
|------------------------|---------------------------|
| Enclosure Type | NEMA 3R |
| Insulation temperature | 356 °F (180 °C) |
| Product certifications | CSA cULus UL listed |

Ordering and shipping details

| | |
|----------|-------------------------|
| Category | 16277 - RESIN LVGP XFMR |
|----------|-------------------------|

| | |
|-----------------------|----------------|
| Discount Schedule | PE2 |
| GTIN | 00785901359562 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 165 |
| Returnability | Y |
| Country of origin | MX |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 1430 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available |
| Product end of life instructions | Need no specific recycling operations |
| California proposition 65 | WARNING: This product can expose you to chemicals including: |
| ----- Substance 1 | Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. |
| ----- More information | For more information go to www.p65warnings.ca.gov |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|