

# 10S4FSS

## TRANSFORMER DRY 1 PHASE 10 KVA 120/240V SECONDARY



### Main

Product or component type	Dry Sealed Transformer
Primary Voltage	600 V
Secondary Voltage	120/240 V
Full Capacity Taps	2 5 % FCBN

### Complementary

Enclosure Code	13B
Phase	1 phase
Primary to Secondary Voltage	600 V : 120/240 V
Power Rating	10 kVA
Temperature rise	115 °C
Height	14.75 in
Width	9.75 in
Depth	11.75 in
Enclosure mounting	Wall mounted
Enclosure material	Stainless steel

### Environment

Enclosure Type	NEMA 3R
Insulation temperature	356 °F (180 °C)
Product certifications	CSA cULus UL listed

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications