

Product data sheet

Specifications



discrete input module Modicon Quantum - 16 inputs - 48 V AC

140DAI44000C

 **Discontinued on:** Jul 12, 2021

 **Discontinued**

Main

Range Of Product	Modicon Quantum automation platform
Product Or Component Type	VAC discrete input modules
Software Name	Concept Unity Pro ProWORX 32
Discrete Input Number	16

Complementary

Group Of Channels	16
Addressing Requirement	1 input word
Discrete Input Voltage	48 V AC
Input Current	11 mA 57...63 Hz 9.3 mA 47...53 Hz
Voltage State 1 Guaranteed	34...56 V AC 57...63 Hz 36...56 V AC 47...53 Hz
Voltage State 0 Guaranteed	0...10 V 57...63 Hz 0...10 V 47...53 Hz
Input Impedance	5600 Ohm capacitive 57...63 Hz 6800 Ohm capacitive 47...53 Hz
Network Frequency Limits	47...63 Hz
Maximum Leakage Current	1.7 mA
Absolute Maximum Input	100 V 1 cycle 56 V continuous 63 V 10 s
Response Time	4.9...0.75 ms x line cycle Off-On 7.3...12.3 ms On-Off
Isolation Between Channels	1780 Vrms for 1 minute
Isolation Between Channels And Bus	1780 Vrms for 1 minute
Bus Current Requirement	180 mA
Maximum Power Dissipation In W	5.5 W
Local Signalling	for bus communication is present (Active) 1 LED (green) for external fault detected (F) 1 LED (red) for input status 16 LEDs (green)
Marking	CE
Module Format	Standard

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Net Weight	0.66 lb(US) (0.3 kg)
------------	----------------------

Environment

Protective Treatment	Conformal coating Humiseal 1A33
Standards	UL 508 CSA C22.2 No 142
Product Certifications	cUL FM Class 1 Division 2
Resistance To Electrostatic Discharge	4 kV contact IEC 801-2 8 kV on air IEC 801-2
Resistance To Electromagnetic Fields	9.14 V/m (10 V/m) 80...2000 MHz IEC 801-3
Ambient Air Temperature For Operation	32...140 °F (0...60 °C)
Ambient Air Temperature For Storage	-40...185 °F (-40...85 °C)
Relative Humidity	95 % without condensation
Operating Altitude	<= 16404.2 ft (5000 m)

Ordering and shipping details

Category	18155-QUANTUM I/O & POWER SUPPLIES
Discount Schedule	PC21
Gtin	3595861135918
Returnability	No
Country Of Origin	FR


Contractual warranty

Warranty	18 months
----------	-----------

Dimensions Drawings

Racks for Modules Mounting

Dimensions of Modules and Racks




- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots

Connections and Schema

48 Vac Discrete Input Module

Wiring Diagram



N/C Not Connected