Product data sheet





Ethernet network TCP/IP module class C30 - FactoryCast configurable

140NOE77111C

Discontinued on: Mar 15, 2022



Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Modicon Quantum automation platform
Product Or Component Type	Ethernet network TCP/IP module
Concept	Transparent Ready
Web Server	Class C30
Web Services	Data editor Rack viewer FactoryCast configurable
Communication Service	Modbus TCP messaging SNMP network management Bandwidth management NTP time synchronization SMTP e-mail notification FDR server I/O scanning Global Data
Communication Port Protocol	Ethernet Modbus TCP/IP
Physical Interface	MT/RJ - 100BASE-FX fiber optic RJ45 - 10BASE-T/100BASE-TX twisted pair
Transmission Rate	10/100 Mbit/s

Complementary

Redundancy	Yes hot standby redundant architecture	
Supply	Via the power supply of the rack	
Marking	CE	
Local Signalling	for 10 Mbps or 100 Mbps data rate (10 MB/100 MB) 1 LED for collision detection (Coll) 1 LED for download mode (Kernel) 1 LED for Ethernet module fault (Fault) 1 LED for Ethernet network status (RUN) 1 LED for full-duplex mode (Fduplex) 1 LED for module ready (Ready) 1 LED for network active (Link) 1 LED for rack operational (Active) 1 LED for transmission/reception activity (TxAct/RxAct) 1 LED	
Current Consumption	750 mA 5 V DC	
Module Format	Standard	
Net Weight	0.76 lb(US) (0.345 kg)	

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ip Degree Of Protection	IP20	
Product Certifications	cUL UL 508	
Standards	CSA C22.2 No 142 FM Class 1 Division 2	
Protective Treatment	Conformal coating Humiseal 1A33	
Resistance To Electrostatic Discharge	4 kV contact IEC 801-2 8 kV on air IEC 801-2	
Resistance To Electromagnetic Fields	nce To Electromagnetic 9.14 V/m (10 V/m) 801000 MHz IEC 801-3	
Ambient Air Temperature For Operation	32140 °F (060 °C)	
Ambient Air Temperature For Storage	ir Temperature For -40185 °F (-4085 °C)	
Relative Humidity	95 % without condensation	
Operating Altitude	<= 14763.78 ft (4500 m)	

Ordering and shipping details

Category	US1PC2118150	
Discount Schedule	PC21	
Gtin	3595862055819	
Returnability	No	
Country Of Origin	FR	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.97 in (5.0 cm)
Package 1 Width	6.50 in (16.5 cm)
Package 1 Length	12.20 in (31.0 cm)
Package 1 Weight	21.13 oz (599.0 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	7
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	10.13 lb(US) (4.593 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
②	Mercury Free	
②	Rohs Exemption Information	Yes

Certifications & Standards


Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

140NOE77111C

Dimensions Drawings

Racks for Modules Mounting

Dimensions of Modules and Racks



- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots