Product data sheet





DIO head-end adaptor Modicon Quantum - 2 Modbus+RS485 twisted pair redundant cu

140NOM21200C

Discontinued on: Mar 15, 2022



Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| Range Of Product | Modicon Quantum automation platform |
|---------------------------|-------------------------------------|
| Product Or Component Type | DIO head-end adaptor |

Complementary

| Product Compatibility | 140CRA21210 140CRA21220 |
|-------------------------|--|
| Number Of Port | Modbus RS232 twisted pair redundant copper Modbus Plus RS485 twisted pair redundant copper |
| Transmission Rate | 1 Mbit/s |
| I/O Words | 30 I/32 O |
| Checks | RAM RAM address Processor Checksum |
| Power Dissipation In W | 4 W |
| Bus Current Requirement | 780 mA |

Environment

| Resistance To Electrostatic Discharge | 4 kV contact IEC 801-2 8 kV on air IEC 801-2 | |
|--|---|--|
| Resistance To Electromagnetic Fields | 9.14 V/m (10 V/m) 802000 MHz IEC 801-3 | |
| Ambient Air Temperature For Operation | 32140 °F (060 °C) | |
| Ambient Air Temperature For Storage | -40185 °F (-4085 °C) | |
| Relative Humidity | 95 % without condensation | |
| Operating Altitude | <= 16404.2 ft (5000 m) | |
| Protective Treatment | Conformal coating Humiseal 1A33 | |
| Standards | UL 508 | |
| Product Certifications | DNV C-tick GL RINA FM Class 1 Division 2 RMRS CSA | |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

GOST

Ordering and shipping details

| Category | US1PC2118150 |
|-------------------|---------------|
| Discount Schedule | PC21 |
| Gtin | 3595861136250 |
| Returnability | No |
| Country Of Origin | FR |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|--------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 1.97 in (5.0 cm) |
| Package 1 Width | 6.50 in (16.5 cm) |
| Package 1 Length | 12.40 in (31.5 cm) |
| Package 1 Weight | 17.92 oz (508.0 g) |

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

| ⊘ | Reach Free Of Svhc | |
|----------|----------------------------|-----|
| ⊘ | Mercury Free | |
| ⊘ | Rohs Exemption Information | Yes |


Certifications & Standards

| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
|---------------------------|---|
| | EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |
| Circularity Profile | End of Life Information |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |

Dimensions Drawings

Racks for Modules Mounting

Dimensions of Modules and Racks



- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots