Product data sheet

Specifications





Ethernet fibre converter SM/LC 2CH - 100 MB

140NRP31201

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Modicon Quantum automation platform
Product Or Component Type	Fibre converter
Optic Fiber Type	Single mode

Complementary

Bus Current Requirement	1000 mA	
Power Dissipation In W	5 W	
Inrush Current	1 A 5 V DC	
Number Of Port	2 fiber optic LC 2 ETHERNET RJ45	
Local Signalling 1 LED green RDY module status 1 LED red ERR internal fault, module failure 1 LED green STS1 channel 1 link status 1 LED green FX1 ACT channel 1 communication status 1 LED green STS2 channel 2 link status 1 LED green FX2 ACT channel 2 communication status		
Wavelength	0.000051575 in (1310 nm)	
Optic Distance Between 2 Transceivers	49212.60 ft (15000 m) 9/125 μm)-158 dBm	
Attenuation	-158 dB 9/125 μm)	
Rise/Fall Time	2.5 ns	
Receiver Sensitivity	- 28 dBm	
Detected Silence	-45 dBm	
Marking	CE	
Material	PC (polycarbonate)	
Width	1.59 in (40.34 mm)	
Height	9.84 in (250 mm)	
Depth	4.09 in (103.85 mm)	
Net Weight	1.22 lb(US) (0.554 kg)	

Environment

Ambient Air Temperature For Operation	32140 °F (060 °C)
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)
Relative Humidity	095 %
Operating Altitude	06561.68 ft (02000 m)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Standards	UL 508 CSA C22.2 No 142 FM Class 1 Division 2
Product Certifications	TÜV Merchant Navy C-tick

Ordering and shipping details

Category	US1PC2118155	
Discount Schedule	PC21	
Gtin	3595864179254	
Returnability	No	
Country Of Origin	US	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.42 in (16.3 cm)
Package 1 Width	1.77 in (4.5 cm)
Package 1 Length	12.28 in (31.2 cm)
Package 1 Weight	21.66 oz (614.0 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	7
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	9.48 lb(US) (4.298 kg)



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes


Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Racks for Modules Mounting

Dimensions of Modules and Racks



- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots