

Product data sheet

Characteristics

150T3HNV

TRFMR DRY 3PH 150KVA 480V-208Y/120V

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 33,348.00 USD



Main

Product	Non-Ventilated Transformer
Enclosure Code	25E
Insulation Temperature	428 °F (220 °C)
Phase	3 phases
Primary Voltage	480 V delta
Power Rating	150 kVA
Secondary Voltage	208Y/120 V
Full Capacity Taps	6 2.5 % 2+ 4-
Temperature Rise	150 °C
Winding Material	Aluminium

Ordering and shipping details

Category	16273 - NON VENT NON RESIN LVGP
Discount Schedule	PE2
GTIN	00785901458982
Nbr. of units in pkg.	1
Package weight(Lbs)	1012
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 4Q2016 Will be compliant on 4Q2016
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------
