Specifications





() Discontinued

## discrete input module Modicon Momentum - 16 Input 200..240 V AC

170ADI74050

() Discontinued on: Oct 9, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

| Range Of Product          | Modicon Momentum automation platform |
|---------------------------|--------------------------------------|
| Product Or Component Type | Discrete inputs base AC              |
| Group Of Channels         | 2 groups of 8 inputs                 |
| Discrete Input Number     | 16 IEC 1131-2 Type 2                 |
| Discrete Input Voltage    | 230 V AC                             |
| Protective Treatment      | TC                                   |

## Complementary

| Discrete Input Logic           | Positive   |
|--------------------------------|--|
| Input Voltage Limits           | 164253 V   |
| Network Frequency              | 4763 Hz  |
| Voltage Range                  | 163253 V   |
| Voltage State 0 Guaranteed     | <= 40 V  |
| Voltage State 1 Guaranteed     | >= 164 V   |
| Current State 0 Guaranteed     | <= 2 mA  |
| Current State 1 Guaranteed     | >= 10 mA   |
| Input Resistance               | 7.5 kOhm 60 Hz<br>9 kOhm 50 Hz   |
| Response Time                  | 13.3 ms 60 Hz from state 0 to state 1<br>13.3 ms 60 Hz from state 1 to state 0 |
| Isolation Between Group        | 1780 V AC  |
| Isolation Botwoon Channels And | 1700.1/ 4.0  |

Isolation Between Channels And 1780 V AC Bus

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

| Terminals Description Plc N°1 | (8)IN_DIS#8<br>(7)IN_DIS#7<br>(5)IN_DIS#7<br>(16)IN_DIS#16<br>(12)IN_DIS#12<br>(2)IN_DIS#2<br>(14)IN_DIS#14<br>(15)IN_DIS#15<br>(N)PW<br>(11)IN_DIS#11<br>(4)IN_DIS#4<br>(9)IN_DIS#9<br>(L1)PW<br>(3)IN_DIS#3<br>(6)IN_DIS#6<br>TB |
|-------------------------------|--|
|                               | (13)IN_DIS#13  |
|                               | (1)IN_DIS#1  |
|                               | (10)IN_DIS#10  |
| Marking                       | CE   |
| Local Signalling              | for channel status 16 LEDs   |
| Current Consumption           | <= 125 mA 230 V AC   |
| Depth                         | 1.87 in (47.5 mm)  |
| Height                        | 5.57 in (141.5 mm)   |
| Width                         | 4.92 in (125 mm)   |
| Net Weight                    |  |

## Environment

| Product Certifications                   | CSA<br>UL                                       |
|--|---|
| Resistance To Electrostatic<br>Discharge | 4 kV contact IEC 801-2<br>8 kV on air IEC 801-2 |
| Resistance To Electromagnetic<br>Fields  | 9.14 V/m (10 V/m) 801000 MHz IEC 801-3          |
| Ambient Air Temperature For<br>Operation | 32140 °F (060 °C)                               |
| Ambient Air Temperature For<br>Storage   | -40185 °F (-4085 °C)                            |
| Relative Humidity                        | 95 % without condensation                       |
| Operating Altitude                       | <= 16404.2 ft (5000 m)                          |

## Ordering and shipping details

| Category          | US1PC3118206  |
|-------------------|---------------|
| Discount Schedule | PC31          |
| Gtin              | 3595861147539 |
| Returnability     | No            |
| Country Of Origin | FR            |

## **Packing Units**

| Unit Type Of Package 1       | PCE                |
|------------------------------|--------------------|
| Number Of Units In Package 1 | 1                  |
| Package 1 Height             | 3.54 in (9.0 cm)   |
| Package 1 Width              | 7.09 in (18.0 cm)  |
| Package 1 Length             | 10.24 in (26.0 cm) |

| Package 1 Weight             | 16.40 oz (465.0 g)      |
|------------------------------|-------------------------|
| Unit Type Of Package 2       | P06                     |
| Number Of Units In Package 2 | 80                      |
| Package 2 Height             | 41.34 in (105.0 cm)     |
| Package 2 Width              | 31.50 in (80.0 cm)      |
| Package 2 Length             | 31.50 in (80.0 cm)      |
| Package 2 Weight             | 100.75 lb(US) (45.7 kg) |

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free


Rohs Exemption Information
Yes

### **Certifications & Standards**

| Reach Regulation            | REACh Declaration  |
|-----------------------------|--|
| Eu Rohs Directive           | Pro-active compliance (Product out of EU RoHS legal scope)   |
| China Rohs Regulation       | China RoHS declaration   |
| Environmental Disclosure    | Product Environmental Profile  |
|                             |  |
| Weee                        | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |
| Weee<br>Circularity Profile |  |


### **Dimensions Drawings**

#### Standard Adapter on a Discrete VAC Base



Mounting and Clearance


#### Mounting on a Wall




#### Connections and Schema

#### **External Wiring Diagrams**

#### 2-Wire Devices



#### **3-Wire Device**



Internal Pin Connections

