

Product data sheet

Characteristics

175DE010

MV FUSE CURRENT LIMIT DIN-E 15 kV 10E-SET OF 3

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 3,214.00 USD



Main

Product or component type	Fuse
Protection technology	Current limiter
Associated fuse rating	10 A E

Complementary

Line Rated Current	600 A
Network frequency	50/60 Hz
[Ur] highest voltage for equipment	15 kV
[Ui] rated insulation voltage	90 V
Type of installation	Indoor
Length	21.1 in
Diameter	3.5 in

Environment

Product certifications	CUL UL listed
------------------------	------------------

Ordering and shipping details

Category	08980 - DIGEST C/LIMITING FUSE KIT
Discount Schedule	PE5B
GTIN	00785901899594
Nbr. of units in pkg.	1
Package weight(Lbs)	17
Returnability	Y
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant Will be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------
