

Product data sheet

Specifications

Acti9 - comb busbar - 3L+N balanced - 9 mm pitch - 18 modules - 80A



19516

⚠ Discontinued on: Jul 12, 2021

⚠ Discontinued

Main

Range	Acti9
Product Or Component Type	Comb busbar
Mounting Mode	Horizontal
Accessory / Separate Part Category	Connection accessory
Lines Description	3L + N
Length In 18 Mm Modules	18

Complementary

Number Of Ways	18 ways N + 3 L (balanced)
Poles Configuration For 1 Way	1 x 3P + N 1 x 3P 3 x 1P + N
Connection Pitch	0.35 in (9 mm)
Connector Type	tooth
Distance Between Way	2.13 in (54 mm)
Marking	N L1 N L2 N L3
Insulation	Insulated
Device Presentation	Cuttable
[Ie] Rated Operational Current	80 A 104 °F (40 °C)
[Ue] Rated Operational Voltage	230 V AC Ph/N 400 V AC Ph/Ph
[Ui] Rated Insulation Voltage	440 V AC IEC 61439-1
[Uimp] Rated Impulse Withstand Voltage	6 kV
Mounting Location	Top tunnel type terminals
9 Mm Pitches	36
Width	12.60 in (320 mm)
Color	Light gray RAL 7035)
Range Compatibility	Acti 9 Acti9 C40 Acti 9 Acti9 C40 Vigi Acti 9 Acti9 ID C40 Multi9 Multi9 N40 Vigi N40 Vigi Acti 9 Acti9 iDPN N Arc Acti 9 Acti9 iARC DPNN Multi9 Multi9 N40

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	EN/IEC 60439-1 IEC 60947-7
Fire Resistance	1760 °F (960 °C) 30 s) IEC 60695-2-1
Pollution Degree	3 IEC 60947-7

Ordering and shipping details

Gtin	3303430195160
------	---------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.18 in (3 cm)
Package 1 Width	1.18 in (3 cm)
Package 1 Length	14.76 in (37.5 cm)
Package 1 Weight	6.70 oz (190 g)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

<div><div>✓</div><div>Reach Free Of Svhc</div></div>	
<div><div>✓</div><div>Toxic Heavy Metal Free</div></div>	
<div><div>✓</div><div>Mercury Free</div></div>	
<div><div>✓</div><div>Rohs Exemption Information</div></div>	<div>Yes</div>
<div>Eu Rohs Directive</div>	<div><div>Compliant</div><div>EU RoHS Declaration</div></div>
<div>China Rohs Regulation</div>	<div><div>China RoHS declaration</div><div>Pro-active China RoHS declaration (out of China RoHS legal scope)</div></div>
<div>Weee</div>	<div>The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.</div>