

# Product data sheet

## Characteristics

# 225T3HNV

## TRANSFORMER DRY 3P 225KVA

### 480V-208Y/120V

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 50,238.00 USD



### Main

|                        |                            |
|------------------------|----------------------------|
| Product                | Non-Ventilated Transformer |
| Enclosure Code         | 30E                        |
| Insulation Temperature | 428 °F (220 °C)            |
| Phase                  | 3 phases                   |
| Primary Voltage        | 480 V delta                |
| Power Rating           | 225 kVA                    |
| Secondary Voltage      | 208Y/120 V                 |
| Full Capacity Taps     | 6 2.5 % 2+ 4-              |
| Temperature Rise       | 150 °C                     |
| Winding Material       | Aluminium                  |

### Ordering and shipping details

|                       |                                 |
|-----------------------|---------------------------------|
| Category              | 16273 - NON VENT NON RESIN LVGP |
| Discount Schedule     | PE2                             |
| GTIN                  | 00785901805267                  |
| Nbr. of units in pkg. | 1                               |
| Package weight(Lbs)   | 1309                            |
| Returnability         | N                               |
| Country of origin     | US                              |

### Offer Sustainability

|                           |  |
|---------------------------|--|
| RoHS (date code: YYWW)    | Will be compliant on 4Q2016<br>Will be compliant on 4Q2016   |
| California proposition 65 | WARNING: This product can expose you to chemicals including:   |
| ----- Substance 1         | Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. |

---

----- More information

For more information go to [www.p65warnings.ca.gov](http://www.p65warnings.ca.gov)

---

### Contractual warranty

---

Warranty period

18 months

---