

2510FF2PG

FHP Manual Starter - Flush Mount - 2P - Toggle Operated - Grn Indicator - 277VAC



Price* : 141.88 USD

2510FF2PG has not been replaced. Please contact your customer care center for more information.



⚠ Discontinued

Main

Product	Single Unit Manual Starter
Type	F
Overload Relay Type	Melting alloy

Complementary

Line Rated Current	16 A
Cable entry	Without
Horsepower Rating	1 hp at 115 V AC 1 hp at 277 V AC 0.75 hp at 115 V DC 0.75 hp at 230 V DC 2 hp at 230 V AC
System Voltage	277 V AC 230 V DC
Number of Poles	2P
Control Unit	Toggle switch
Phase	1 phase
Pilot Light	Green indicator
Reset	Manual
Motor starter type	Non reversing
Electrical connection	Screw clamp terminals
Wire Gauge	AWG 14...AWG 12 (copper)
Height	4.5 in
Width	2.75 in
Depth	2.19 in

Environment

Product certifications	UL listed file E42243 CCN NLRV
------------------------	--------------------------------

NEMA Enclosure Rating	Not rated (flush plate) sheet steel standard size
-----------------------	---------------------------------------------------

Ordering and shipping details

Category	21101 - 2510,2511,2512 F
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------