

# Product data sheet

## Characteristics

# 2510FG2PG

## FHP Manual Starter - NEMA 1 - 2P - Toggle Operated - Green Indicator - 277VAC

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 150.25 USD



### Main

Product	Single Unit Manual Starter
Type	F
Overload Relay Type	Melting alloy

### Complementary

Line Rated Current	16 A
Cable entry	0.5" and 0.75" knock-outs (top and bottom)
Horsepower Rating	1 hp at 115 V AC 1 hp at 277 V AC 0.75 hp at 115 V DC 0.75 hp at 230 V DC 2 hp at 230 V AC
System Voltage	277 V AC 230 V DC
Number of Poles	2P
Control Unit	Toggle switch
Phase	1 phase
Pilot Light	Green indicator
Reset	Manual
Motor starter type	Non reversing
Electrical connection	Screw clamp terminals
Wire Gauge	AWG 14...AWG 12 (copper)
Height	4.25 in
Width	2.44 in
Depth	2.75 in

## Environment

Product certifications	UL listed file E42243 CCN NLRV CSA LR25490 class 3211 05
NEMA Enclosure Rating	NEMA 1 plastic standard size

## Ordering and shipping details

Category	21101 - 2510,2511,2512 F
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	0.8100000000000005
Returnability	N
Country of origin	MX

## Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------