

# Product data sheet

Specifications

SQUARE D



## Duplex Manual Starter NEMA 1 - 2P Starter-Toggle-1 Selector-Grn Indicator-277VAC

2510FG72PG

⚠ Discontinued on: Oct 12, 2021

⚠ Discontinued

### Main

Product	Duplex Unit Manual Starter
Type	F
Overload Relay Type	Melting alloy

### Complementary

Current Rating	16 A
Cable Entry	0.5" and 0.75" knock-outs (top and bottom)
Horsepower Rating	1 hp 115 V AC 1 hp 277 V AC 0.75 hp 115 V DC 0.75 hp 230 V DC 2 hp 230 V AC
Voltage Rating	277 V AC 230 V DC
Number Of Poles	2P
Control Unit	Toggle switch
Number Of Phases	1 phase
Pilot Light	Green indicator
Reset	Manual
Motor Starter Type	Non reversing
Electrical Connection	Screw clamp terminals
Wire Gauge	AWG 14...AWG 12 copper
Height	4.25 in (107.95 mm)
Width	2.44 in (61.98 mm)
Depth	2.88 in (73.15 mm)

### Environment

Product Certifications	UL listed file E42243 CCN NLRV CSA LR25490 class 3211 05
Nema Enclosure Rating	NEMA 1 Plastic standard size

### Ordering and shipping details

Category	21101-2510,2511,2512 F
Discount Schedule	CP1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Returnability	No
Country Of Origin	MX

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

### Contractual warranty

Warranty	18 months
----------	-----------