

Product data sheet

Characteristics

2510FR2

FHP Manual Starter - NEMA 7&9 - 1 Conduit Opening - 2P - No Indicator - 277VAC

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 381.38 USD



Main

Product	Single Unit Manual Starter
Type	F
Overload Relay Type	Melting alloy

Complementary

Line Rated Current	16 A
Cable entry	0.75 NPT (bottom)
Horsepower Rating	1 hp at 115 V AC 1 hp at 277 V AC 0.75 hp at 115 V DC 0.75 hp at 230 V DC 2 hp at 230 V AC
System Voltage	277 V AC 230 V DC
Number of Poles	2P
Control Unit	Toggle switch (with lock-off)
Phase	1 phase
Pilot Light	No indicator
Reset	Manual
Motor starter type	Non reversing
Electrical connection	Screw clamp terminals
Wire Gauge	AWG 14...AWG 12 (copper)
Height	6.36 in
Width	3.95 in
Depth	4.35 in

Environment

Product certifications	UL listed file E42243 CCN NLRV CSA LR25490 class 3211 05
NEMA Enclosure Rating	NEMA 3R/7/9 cast aluminium standard size

Ordering and shipping details

Category	21101 - 2510,2511,2512 F
Discount Schedule	CP1
GTIN	00785901554219
Nbr. of units in pkg.	1
Package weight(Lbs)	3.6000000000000001
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------