

Product data sheet

Characteristics

2510FW2PG

FHP Manual Starter - NEMA 4 - 1 Conduit Opening - 2P - Green Indicator - 277VAC

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 471.85 USD



Main

Product	Single Unit Manual Starter
Type	F
Overload Relay Type	Melting alloy

Complementary

Line Rated Current	16 A
Cable entry	0.75 NPT (bottom)
Horsepower Rating	1 hp at 115 V AC 1 hp at 277 V AC 0.75 hp at 115 V DC 0.75 hp at 230 V DC 2 hp at 230 V AC
System Voltage	277 V AC 230 V DC
Number of Poles	2P
Control Unit	Toggle switch (with lock-off)
Phase	1 phase
Pilot Light	Green indicator
Reset	Manual
Motor starter type	Non reversing
Electrical connection	Screw clamp terminals
Wire Gauge	AWG 14...AWG 12 (copper)
Height	4.38 in
Width	3 in
Depth	4.56 in

Environment

Product certifications	UL listed file E42243 CCN NLRV CSA LR25490 class 3211 05
NEMA Enclosure Rating	NEMA 4 die cast zinc alloy standard size

Ordering and shipping details

Category	21101 - 2510,2511,2512 F
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	2.9900000000000002
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------