

# Product data sheet

## Characteristics

# 2510K1

## Manual Switch - NEMA 1 - 3P - Toggle Operated - No Indicator - 600VAC

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\*\* : 156.57 USD



! Discontinued

### Main

Product	Single Unit Manual Switch
Type	K

### Complementary

Current Rating	30 A
Cable Entry	0.5" and 0.75" knock-outs (top and bottom)
Horsepower Rating	2 hp 115 V AC 2 hp 230 V AC 3 hp 460 V AC 3 hp 575 V AC 1 hp 90 V DC 2 hp 115 V DC 1.5 hp 230 V DC
Maximum Voltage Rating	600 V AC 230 V DC
Number of Poles	3P
Control Unit Type	Toggle
Number of Phases	1 phase
Pilot Light	No indicator
Starter Type	Non reversing
Electrical Connection	Screw clamp terminals
Wire Gauge	AWG 14...AWG 10 copper
Height	107.95 mm (4.25 in)
Width	61.98 mm (2.44 in)
Depth	69.85 mm (2.75 in)

### Environment

Certifications	UL listed file E42243 CCN NLRV
----------------	--------------------------------

---

NEMA Enclosure Rating	NEMA 1 painted sheet steel standard size
-----------------------	--

---

### Ordering and shipping details

---

Category	21102 - 2510,2511,2512 K
Discount Schedule	CP1
GTIN	00785901006145
Package weight(Lbs)	0.41 kg (0.91 lb(US))
Returnability	No
Country of origin	MX

---

### Offer Sustainability

---

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

---

### Contractual warranty

---

Warranty	18 months
----------	-----------

---

### 2510K1 is replaced by:

---



#### 2510K Manual Switches 2510KG2

Manual switch, 3 P, 30 amp, toggle operated, no pilot light, 600 VAC, NEMA 1 enclosure

Qty 1

Reason for Substitution: End of life | Substitution date: 01 January 2017

---