

Product data sheet

Characteristics

2510KG5

Manual Switch - NEMA 1 - 2P - Toggle Operated - No Indicator - 600VAC

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 82.01 USD



Main

Product	Single Unit Manual Switch
Type	K

Complementary

Line Rated Current	30 A
Cable Entry	0.5" and 0.75" knock-outs (top and bottom)
Horsepower Rating	2 hp at 115 V AC 1 hp at 90 V DC 2 hp at 115 V DC 1.5 hp at 230 V DC 10 hp at 575 V AC 3 hp at 230 V AC 7.5 hp at 460 V AC
System Voltage	600 V AC 230 V DC
Number of Poles	2P
Control Unit Type	Toggle
Phase	1 phase
Pilot Light	No indicator
Starter Type	Non reversing
Electrical Connection	Screw clamp terminals
Wire Gauge	AWG 14...AWG 10 (copper)
Height	4.25 in
Width	2.44 in
Depth	2.75 in

Environment

Certifications	CE
----------------	----

UL listed file E42243 CCN NLRV
CSA LR25490 class 3211 05

NEMA Enclosure Rating	NEMA 1 plastic standard size
-----------------------	------------------------------

Ordering and shipping details

Category	21102 - 2510,2511,2512 K
Discount Schedule	CP1
GTIN	00785901192695
Nbr. of units in pkg.	1
Package weight(Lbs)	0.8499999999999998
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1545 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------