

Product data sheet

Specifications

SQUARE D



Manual switch, Type K, single unit, 600VAC, 2 pole, 30A, toggle switch, plastic enclosure

2510KG5B

Discontinued on: Sep 15, 2023

To be end-of-service on: Dec 31, 2024

Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| | |
|---------|---------------------------|
| Product | Single Unit Manual Switch |
| Type | K |

Complementary

| | |
|------------------------|---|
| Current Rating | 30 A |
| Cable Entry | 0.5" and 0.75" knock-outs (top and bottom) |
| Horsepower Rating | 2 hp 115 V AC 1 hp 90 V DC 2 hp 115 V DC 1.5 hp 230 V DC 10 hp 575 V AC 3 hp 230 V AC 7.5 hp 460 V AC |
| Maximum Voltage Rating | 600 V AC 230 V DC |
| Number Of Poles | 2P |
| Control Unit Type | Toggle |
| Number Of Phases | 1 phase |
| Pilot Light | Red indicator, 230 V |
| Starter Type | Non reversing |
| Electrical Connection | Screw clamp terminals |
| Wire Gauge | AWG 14...AWG 10 copper |
| Height | 4.25 in (107.95 mm) |
| Width | 2.44 in (61.98 mm) |
| Depth | 2.75 in (69.85 mm) |

Environment

| | |
|-----------------------|---|
| Certifications | UL listed file E42243 CCN NLRV CSA LR25490 class 3211 05 |
| Nema Enclosure Rating | NEMA 1 Plastic standard size |

Ordering and shipping details

| | |
|----------|--------------|
| Category | US10CP121102 |
|----------|--------------|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|-------------------|--------------|
| Discount Schedule | 0CP1 |
| Gtin | 785901342328 |
| Returnability | No |
| Country Of Origin | MX |

Packing Units

| | |
|------------------------------|----------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 5.00 in (12.7 cm) |
| Package 1 Width | 2.50 in (6.35 cm) |
| Package 1 Length | 3.00 in (7.62 cm) |
| Package 1 Weight | 21.87 oz (620.061 g) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Pvc Free

| | |
|---------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Not compliant |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |