

# Product data sheet

## Characteristics

# 2510KGJ1B

Manual Switch - NEMA 1 Oversized - 2P - Toggle Operated -Red Indicator - 600VAC

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 160.75 USD



### Main

Product	Single Unit Manual Switch
Type	K

### Complementary

Line Rated Current	30 A
Cable Entry	0.5" and 0.75" knock-outs (top and bottom)
Horsepower Rating	3 hp at 460 V AC 2 hp at 230 V AC 2 hp at 115 V AC 3 hp at 575 V AC 1 hp at 90 V DC 2 hp at 115 V DC 1.5 hp at 230 V DC
System Voltage	600 V AC 230 V DC
Number of Poles	2P
Control Unit Type	Toggle
Phase	1 phase
Pilot Light	Red indicator 230 V
Starter Type	Non reversing
Electrical Connection	Screw clamp terminals
Wire Gauge	AWG 14...AWG 10 (copper)
Height	4.25 in
Width	2.88 in
Depth	2.75 in

### Environment

Certifications	CE
----------------	----

UL listed file E42243 CCN NLRV  
CSA LR25490 class 3211 05

NEMA Enclosure Rating	NEMA 1 painted sheet steel oversized
-----------------------	--------------------------------------

### Ordering and shipping details

Category	21102 - 2510,2511,2512 K
Discount Schedule	CP1
GTIN	00785901005674
Nbr. of units in pkg.	1
Package weight(Lbs)	1.5600000000000001
Returnability	N
Country of origin	MX

### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1545 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------