

2510KGJ3A

Manual Switch - NEMA 1 Oversized - 2P - Key Operated - Red Indicator - 600VAC



Price* : 188.06 USD



2510KGJ3A has not been replaced. Please contact your customer care center for more information.

Main

Product	Single Unit Manual Switch
Type	K

Complementary

Line Rated Current	30 A
Cable Entry	0.5" and 0.75" knock-outs (top and bottom)
Horsepower Rating	3 hp at 460 V AC 2 hp at 230 V AC 2 hp at 115 V AC 3 hp at 575 V AC 1 hp at 90 V DC 2 hp at 115 V DC 1.5 hp at 230 V DC
System Voltage	600 V AC 230 V DC
Number of Poles	2P
Control Unit Type	Key
Phase	1 phase
Pilot Light	Red indicator 230 V
Starter Type	Non reversing
Electrical Connection	Screw clamp terminals
Wire Gauge	AWG 14...AWG 10 (copper)
Height	4.25 in
Width	2.88 in
Depth	2.75 in

Environment

Certifications	CE UL listed file E42243 CCN NLRV
----------------	--------------------------------------

NEMA Enclosure Rating	NEMA 1 painted sheet steel oversized
-----------------------	--------------------------------------

Ordering and shipping details

Category	21102 - 2510,2511,2512 K
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	0.800000000000000004
Returnability	N
Country of origin	MX

Contractual warranty

Warranty period	18 months
-----------------	-----------
