


2510KGJ4C

Manual Switch - NEMA 1 Oversized - 3P - Key Operated - Red Indicator - 600VAC



Price* : 277.36 USD



2510KGJ4C has not been replaced. Please contact your customer care center for more information.

Main

Product	Single Unit Manual Switch
Type	K

Complementary

Line Rated Current	30 A
Cable Entry	0.5" and 0.75" knock-outs (top and bottom)
Horsepower Rating	2 hp at 115 V AC 1 hp at 90 V DC 2 hp at 115 V DC 1.5 hp at 230 V DC 7.5 hp at 230 V AC 10 hp at 460 V AC 10 hp at 575 V AC
System Voltage	600 V AC 230 V DC
Number of Poles	3P
Control Unit Type	Key
Phase	3 phases
Pilot Light	Red indicator 440...600 V
Starter Type	Non reversing
Electrical Connection	Screw clamp terminals
Wire Gauge	AWG 14...AWG 10 (copper)
Height	4.25 in
Width	2.88 in
Depth	2.75 in

Environment

Certifications	CE UL listed file E42243 CCN NLRV
----------------	--------------------------------------

NEMA Enclosure Rating	NEMA 1 painted sheet steel oversized
-----------------------	--------------------------------------

Ordering and shipping details

Category	21102 - 2510,2511,2512 K
Discount Schedule	CP1
GTIN	00785901931959
Nbr. of units in pkg.	1
Package weight(Lbs)	0.8000000000000004
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------