


Product data sheet

Specifications

SQUARE D



Manual Switch - SS Flush - 2P - Toggle Operated - Green Indicator - 600VAC

2510KS1AG

! Discontinued

Main

Product	Single Unit Manual Switch
Type	K

Complementary

Current Rating	30 A
Horsepower Rating	2 hp 115 V AC 2 hp 230 V AC 3 hp 460 V AC 3 hp 575 V AC 1 hp 90 V DC 2 hp 115 V DC 1.5 hp 230 V DC
Maximum Voltage Rating	600 V AC 230 V DC
Number Of Poles	2P
Control Unit Type	Toggle
Number Of Phases	1 phase
Pilot Light	Green indicator, 115 V
Starter Type	Non reversing
Electrical Connection	Screw clamp terminals
Wire Gauge	AWG 14...AWG 10 copper
Height	4.5 in (114.30 mm)
Width	2.75 in (69.85 mm)
Depth	2.5 in (63.50 mm)

Environment

Certifications	UL listed file E42243 CCN NLRV CSA LR25490 class 3211 05
Nema Enclosure Rating	Not rated (flush plate) Stainless Steel standard size

Ordering and shipping details

Category	21102-2510,2511,2512 K
Discount Schedule	CP1
Gtin	00785901738831
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Country Of Origin	MX
-------------------	----

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	8.00 oz (226.796 g)

Contractual warranty

Warranty	18 months
----------	-----------