

Product data sheet

Characteristics

2510KS2

Manual Switch - SS Flush - 3P - Toggle Operated - No Indicator - 600VAC

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 156.57 USD



Main

Product	Single Unit Manual Switch
Type	K

Complementary

Line Rated Current	30 A
Horsepower Rating	2 hp at 115 V AC 1 hp at 90 V DC 2 hp at 115 V DC 1.5 hp at 230 V DC 7.5 hp at 230 V AC 10 hp at 460 V AC 10 hp at 575 V AC
System Voltage	600 V AC 230 V DC
Number of Poles	3P
Control Unit Type	Toggle
Phase	3 phases
Pilot Light	No indicator
Starter Type	Non reversing
Electrical Connection	Screw clamp terminals
Wire Gauge	AWG 14...AWG 10 (copper)
Height	4.5 in
Width	2.75 in
Depth	2.5 in

Environment

Certifications	CE UL listed file E42243 CCN NLRV
----------------	--------------------------------------

NEMA Enclosure Rating	Not rated (flush plate) stainless steel standard size
-----------------------	---

Ordering and shipping details

Category	21102 - 2510,2511,2512 K
Discount Schedule	CP1
GTIN	00785901554684
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5100000000000001
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1545 - Schneider Electric declaration of conformity
------------------------	---

 [Schneider Electric declaration of conformity](#)

California proposition 65	WARNING: This product can expose you to chemicals including:
---------------------------	--

----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
-------------------	--

----- More information	For more information go to www.p65warnings.ca.gov
------------------------	---

Contractual warranty

Warranty period	18 months
-----------------	-----------