

2510KW1AGH

Manual Switch - NEMA 4 - 2P - Toggle Operated -
Green Indicator - 600VAC



Price* : 458.00 USD



2510KW1AGH has not been replaced. Please contact your customer care center for more information.

Discontinued

Main

Product or component type	Single Unit Manual Switch
Range of product	K

Complementary

Line Rated Current	30 A
Cable entry	0.75 NPT (top and bottom)
Motor power hp	3 hp at 460 V AC 2 hp at 230 V AC 2 hp at 115 V AC 3 hp at 575 V AC 1 hp at 90 V DC 2 hp at 115 V DC 1.5 hp at 230 V DC
System Voltage	600 V AC 230 V DC
Poles description	2P
Control type	Toggle
Phase	1 phase
Local signalling	Green indicator 115 V
Motor starter type	Non reversing
Electrical connection	Screw clamp terminals
AWG gauge	AWG 14...AWG 10 (copper)
Height	4.38 in
Width	3 in
Depth	4.56 in

Environment

Product certifications	CE UL listed file E42243 CCN NLRV
------------------------	--------------------------------------

NEMA degree of protection	NEMA 4 die cast zinc alloy standard size
---------------------------	------------------------------------------

Ordering and shipping details

Category	21102 - 2510,2511,2512 K
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	2.8000000000000003
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------