

2510KW5H

Manual Switch - NEMA 4 - 2P - Toggle Operated -
No Indicator - 600VAC



Price* : 362.74 USD

2510KW5H has not been replaced. Please contact your customer care center for more information.



ⓘ Discontinued

Main

| | |
|---------|---------------------------|
| Product | Single Unit Manual Switch |
| Type | K |

Complementary

| | |
|-----------------------|--|
| Line Rated Current | 30 A |
| Cable Entry | 0.75 NPT (top and bottom) |
| Horsepower Rating | 2 hp at 115 V AC 1 hp at 90 V DC 2 hp at 115 V DC 1.5 hp at 230 V DC 10 hp at 575 V AC 3 hp at 230 V AC 7.5 hp at 460 V AC |
| System Voltage | 600 V AC 230 V DC |
| Number of Poles | 2P |
| Control Unit Type | Toggle |
| Phase | 1 phase |
| Pilot Light | No indicator |
| Starter Type | Non reversing |
| Electrical Connection | Screw clamp terminals |
| Wire Gauge | AWG 14...AWG 10 (copper) |
| Height | 4.38 in |
| Width | 3 in |
| Depth | 4.25 in |

Environment

| | |
|----------------|--------------------------------------|
| Certifications | CE UL listed file E42243 CCN NLRV |
|----------------|--------------------------------------|

| | |
|-----------------------|--|
| NEMA Enclosure Rating | NEMA 4 die cast zinc alloy standard size |
|-----------------------|--|

Ordering and shipping details

| | |
|-----------------------|--------------------------|
| Category | 21102 - 2510,2511,2512 K |
| Discount Schedule | CP1 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 2.8000000000000003 |
| Returnability | N |
| Country of origin | MX |

Offer Sustainability

| | |
|------------------------|--|
| RoHS (date code: YYWW) | Will be compliant Will be compliant |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|