

# Product data sheet

## Characteristics

# 2510KW6CH

## Manual Switch - NEMA 4 - 3P - Toggle Operated - Red Indicator - 600VAC

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 557.05 USD



### Main

Product	Single Unit Manual Switch
Type	K

### Complementary

Line Rated Current	30 A
Cable Entry	0.75 NPT (top and bottom)
Horsepower Rating	2 hp at 115 V AC 1 hp at 90 V DC 2 hp at 115 V DC 1.5 hp at 230 V DC 7.5 hp at 230 V AC 15 hp at 460 V AC 20 hp at 575 V AC
System Voltage	600 V AC 230 V DC
Number of Poles	3P
Control Unit Type	Toggle
Phase	3 phases
Pilot Light	Red indicator 440...600 V
Starter Type	Non reversing
Electrical Connection	Screw clamp terminals
Wire Gauge	AWG 14...AWG 10 (copper)
Height	4.38 in
Width	3 in
Depth	4.56 in

### Environment

Certifications	CE
----------------	----

Mar 26, 2019

UL listed file E42243 CCN NLRV  
CSA LR25490 class 3211 05

NEMA Enclosure Rating	NEMA 4 die cast zinc alloy standard size
-----------------------	--

### Ordering and shipping details

Category	21102 - 2510,2511,2512 K
Discount Schedule	CP1
GTIN	00785901717782
Nbr. of units in pkg.	1
Package weight(Lbs)	3.48
Returnability	N
Country of origin	MX

### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1545 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------