

Product data sheet

Characteristics

2510MBA1V02P11

Manual Starter - NEMA 12 - 2P - Size M0 - Red Indicator - 600VAC

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 497.38 USD



Main

Product	Manual Starter
Type	M
NEMA Size	M-0

Complementary

Control Unit	Push-button
Pilot Light	Red indicator, 120 V
Horsepower Rating	2 hp at 230 V AC 1 phase 1 hp at 115 V AC 1 phase
System Voltage	600 V AC
Number of Poles	2P
Starter Type	Non reversing
Electrical Connection	Pressure wire clamp
Overload Relay Type	Melting alloy
Number of Thermal Units Required	1
Wire Gauge	AWG 14...AWG 8 (copper)
Auxiliary Contacts	Without
Height	10.92 in
Width	5.78 in
Depth	5.76 in

Environment

Certifications	UL listed file E42243 CCN NLRV CSA LR60905 class 3211 05
NEMA Enclosure Rating	NEMA 12 painted sheet steel

Ordering and shipping details

Category	21103 - 2510,2511,2512 M,T
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	8.730000000000004
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------