

Product data sheet

Specifications

SQUARE D



Manual Starter - NEMA 12 - 2P - Size M0 - No Indicator-NC Aux Contact - 600VAC

2510MBA1X2

! Discontinued

Main

Product	Manual Starter
Type	M
Nema Size	M-0

Complementary

Control Unit	Push-button
Pilot Light	No indicator
Horsepower Rating	1 hp 115 V AC, 1 phase 2 hp 230 V AC, 1 phase
Voltage Rating	600 V AC
Number Of Poles	2P
Starter Type	Non reversing
Electrical Connection	Pressure wire clamp
Overload Relay Type	Melting alloy
Number Of Thermal Units Required	1
Wire Gauge	AWG 14...AWG 8 copper
Auxiliary Contacts	1 NC
Height	10.92 in (277.37 mm)
Width	5.78 in (146.81 mm)
Depth	5.76 in (146.30 mm)

Environment

Certifications	UL listed file E42243 CCN NLRV CSA LR60905 class 3211 05
Nema Enclosure Rating	NEMA 12 painted sheet steel

Ordering and shipping details

Category	21103-2510,2511,2512 M,T
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	8.00 lb(US) (3.629 kg)

Contractual warranty

Warranty	18 months
----------	-----------