



Price\* : 363.00 USD



2510MBA1Y76 has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

### Main

Contacteur application	Non-reversing
Device short name	M
Enclosure type	Enclosure dust and damp proof indoor

### Complementary

Control type	Push-button
Depth	5.76 in
Device mounting	Surface
Electrical connection	Pressure wire clamp
Height	10.75 in
Motor power hp	1 hp 115 V AC 2 hp 230 V AC
NEMA size	M-0
Network number of phases	1 phase
Number of poles	2
Number of thermal units required	1
Permissible voltage	<= 600 V AC <= 250 V DC
Width	5.78 in

### Environment

NEMA degree of protection	NEMA 12
Product certifications	UL listed file E42243 CCN NLRV CSA LR60905 class 3211 05

### Ordering and shipping details

Category	21103 - 2510,2511,2512 M,T
Discount Schedule	CP1

GTIN	00785901332404
Nbr. of units in pkg.	1
Package weight(Lbs)	6.9699999999999998
Returnability	N
Country of origin	MX

**Offer Sustainability**

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

**Contractual warranty**

Warranty period	18 months
-----------------	-----------