

# Product data sheet

## Characteristics

# 2510MBA2V06P11X1

Manual Starter - NEMA 12 - 3P - Size M0 - Red Indicator-NO Aux Contact - 600VAC

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\*\* : 650.03 USD



2510MBA2V06P11X1 has not been replaced. Please contact your customer care center for more information.

⚠ Discontinued

### Main

Product	Manual Starter
Type	M
NEMA Size	M-0

### Complementary

Control Unit	Push-button
Pilot Light	Red indicator, 480 V
Horsepower Rating	3 hp at 200...230 V AC 3 phases 5 hp at 380...575 V AC 3 phases
System Voltage	600 V AC
Number of Poles	3P
Starter Type	Non reversing
Electrical Connection	Pressure wire clamp
Overload Relay Type	Melting alloy
Number of Thermal Units Required	3
Wire Gauge	AWG 14...AWG 8 (copper)
Auxiliary Contacts	1 NO
Height	10.92 in
Width	5.78 in
Depth	5.76 in

### Environment

Certifications	UL listed file E42243 CCN NLRV CSA LR60905 class 3211 05
NEMA Enclosure Rating	NEMA 12 painted sheet steel

## Ordering and shipping details

Category	21103 - 2510,2511,2512 M,T
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	7.5
Returnability	N
Country of origin	MX

## Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant <a href="#">Will not be compliant</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------