

Product data sheet

Characteristics

2510MBA2X1

Manual Starter - NEMA 12 - 3P - Size M0 - No Indicator-NO Aux Contact - 600VAC

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 534.03 USD



Main

| | |
|-----------|----------------|
| Product | Manual Starter |
| Type | M |
| NEMA Size | M-0 |

Complementary

| | |
|----------------------------------|--|
| Control Unit | Push-button |
| Pilot Light | No indicator |
| Horsepower Rating | 3 hp at 200...230 V AC 3 phases 5 hp at 380...575 V AC 3 phases |
| System Voltage | 600 V AC |
| Number of Poles | 3P |
| Starter Type | Non reversing |
| Electrical Connection | Pressure wire clamp |
| Overload Relay Type | Melting alloy |
| Number of Thermal Units Required | 3 |
| Wire Gauge | AWG 14...AWG 8 (copper) |
| Auxiliary Contacts | 1 NO |
| Height | 10.92 in |
| Width | 5.78 in |
| Depth | 5.76 in |

Environment

| | |
|-----------------------|---|
| Certifications | UL listed file E42243 CCN NLRV CSA LR60905 class 3211 05 |
| NEMA Enclosure Rating | NEMA 12 painted sheet steel |

Ordering and shipping details

| | |
|-----------------------|----------------------------|
| Category | 21103 - 2510,2511,2512 M,T |
| Discount Schedule | CP1 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 8.410000000000001 |
| Returnability | N |
| Country of origin | MX |

Offer Sustainability

| | |
|----------------------------|--|
| RoHS (date code: YYWW) | Will not be compliant Will not be compliant |
| California proposition 65 | WARNING: This product can expose you to chemicals including: |
| - - - - - Substance 1 | Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. |
| - - - - - More information | For more information go to www.p65warnings.ca.gov |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|