

2510MBA4

Manual Starter - NEMA 12 - 2P - Size M0 - No Indicator - 250VDC



Price* : 381.37 USD



2510MBA4 has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

Main

Product	Manual Starter
Type	M
NEMA Size	M-0

Complementary

Control Unit	Push-button
Pilot Light	No indicator
Horsepower Rating	1.5 hp at 230 V DC 1 hp at 115 V DC
System Voltage	250 V DC
Number of Poles	2P
Starter Type	Non reversing
Electrical Connection	Pressure wire clamp
Overload Relay Type	Melting alloy
Number of Thermal Units Required	1
Wire Gauge	AWG 14...AWG 8 (copper)
Auxiliary Contacts	Without
Height	10.92 in
Width	5.78 in
Depth	5.76 in

Environment

Certifications	UL listed file E42243 CCN NLRV CSA LR60905 class 3211 05
NEMA Enclosure Rating	NEMA 12 painted sheet steel

Ordering and shipping details

Category	21103 - 2510,2511,2512 M,T
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	7.5
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------