

Product data sheet

Characteristics

2510MBG1V02P11X1

Manual Starter - NEMA 1 - Buttons - 2P - Size M0 - Red Ind-NO Aux Cont - 600VAC

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 492.34 USD



Main

Product	Manual Starter
Type	M
NEMA Size	M-0

Complementary

Control Unit	Push-button
Pilot Light	Red indicator, 120 V
Horsepower Rating	2 hp at 230 V AC 1 phase 1 hp at 115 V AC 1 phase
System Voltage	600 V AC
Number of Poles	2P
Starter Type	Non reversing
Electrical Connection	Pressure wire clamp
Overload Relay Type	Melting alloy
Number of Thermal Units Required	1
Wire Gauge	AWG 14...AWG 8 (copper)
Auxiliary Contacts	1 NO
Height	8.63 in
Width	5 in
Depth	4.13 in

Environment

Certifications	UL listed file E42243 CCN NLRV CSA LR60905 class 3211 05
NEMA Enclosure Rating	NEMA 1 painted sheet steel

Ordering and shipping details

Category	21103 - 2510,2511,2512 M,T
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	8
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
------------------------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------