

Product data sheet

Specifications

SQUARE D



Special Manual Starter - NEMA 1 - 3P - Size M0 - No Indicator - 600VAC

2510MBG2Y76

Discontinued

Main

| | |
|-----------|----------------|
| Product | Manual Starter |
| Type | M |
| Nema Size | M-0 |

Complementary

| | |
|-----------------------|------------------------------|
| Control Unit | Push-button |
| Pilot Light | No indicator |
| Horsepower Rating | 3 hp 200...230 V AC, 3 phase |
| Voltage Rating | 600 V AC |
| Number Of Poles | 3P |
| Starter Type | Non reversing |
| Electrical Connection | Pressure wire clamp |
| Wire Gauge | AWG 14...AWG 8 copper |
| Auxiliary Contacts | Without |
| Height | 8.63 in (219.20 mm) |
| Width | 5 in (127.00 mm) |
| Depth | 4.13 in (104.90 mm) |

Environment

| | |
|-----------------------|---|
| Certifications | UL listed file E42243 CCN NLRV CSA LR60905 class 3211 05 |
| Nema Enclosure Rating | NEMA 1 painted sheet steel |

Ordering and shipping details

| | |
|-------------------|--------------------------|
| Category | 21103-2510,2511,2512 M,T |
| Discount Schedule | CP1 |
| Returnability | No |
| Country Of Origin | MX |

Packing Units

| | |
|------------------------------|-----|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------|------------------------|
| Package 1 Weight | 4.00 lb(US) (1.814 kg) |
|------------------|------------------------|

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|