

Product data sheet

Characteristics

2510MBR1

Manual Starter - NEMA 7&9 - 2P - Size M0 - 600VAC

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 1034.30 USD



Main

Product or component type	Manual Starter
Range of product	M
NEMA size	M-0

Complementary

Control type	Push-button
Local signalling	No indicator
Motor power hp	2 hp at 230 V AC 1 phase 1 hp at 115 V AC 1 phase
System Voltage	600 V AC
Poles description	2P
Motor starter type	Non reversing
Electrical connection	Pressure wire clamp
Thermal overload type	Melting alloy
Number of thermal units required	1
AWG gauge	AWG 14...AWG 8 (copper)
Auxiliary contact composition	Without
Height	10.5 in
Width	6 in
Depth	6.13 in

Environment

Product certifications	UL listed file E58760 CCN NPXZ CSA LR26817 class 3218 04
NEMA degree of protection	NEMA 7/9 cast iron

Ordering and shipping details

Category	21103 - 2510,2511,2512 M,T
Discount Schedule	CP1
GTIN	00785901800538
Nbr. of units in pkg.	1
Package weight(Lbs)	31.02
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------