

Product data sheet

Characteristics

2510MBT1

Manual Starter - NEMA 4X/7/9 - 2P - Size M0 - 600VAC

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 1,291.42 USD



Main

Product	Manual Starter
Type	M
NEMA Size	M-0

Complementary

Control Unit	Push-button
Pilot Light	No indicator
Horsepower Rating	2 hp at 230 V AC 1 phase 1 hp at 115 V AC 1 phase
System Voltage	600 V AC
Number of Poles	2P
Starter Type	Non reversing
Electrical Connection	Pressure wire clamp
Overload Relay Type	Melting alloy
Number of Thermal Units Required	1
Wire Gauge	AWG 14...AWG 8 (copper)
Auxiliary Contacts	Without
Height	10.5 in
Width	6 in
Depth	6.13 in

Environment

Certifications	UL listed file E58760 CCN NPXZ CSA LR26817 class 3218 04
NEMA Enclosure Rating	NEMA 7/9 NEMA 4X cast iron

Ordering and shipping details

Category	21103 - 2510,2511,2512 M,T
Discount Schedule	CP1
GTIN	00785901878155
Nbr. of units in pkg.	1
Package weight(Lbs)	25.66
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------