

Product data sheet

Specifications

SQUARE D



Manual Starter - NEMA 1 - Buttons - 3P - Size M1-Red Ind-NO Aux Contact 600VAC

2510MCG3V08P11X1

Discontinued

Main

Product	Manual Starter
Type	M
Nema Size	M-1

Complementary

Control Unit	Push-button
Pilot Light	Red indicator, 208 V
Horsepower Rating	7.5 hp 200...230 V AC, 3 phase 10 hp 380...575 V AC, 3 phase
Voltage Rating	600 V AC
Number Of Poles	3P
Starter Type	Non reversing
Electrical Connection	Pressure wire clamp
Overload Relay Type	Melting alloy
Number Of Thermal Units Required	3
Wire Gauge	AWG 14...AWG 8 copper
Auxiliary Contacts	1 NO
Height	8.63 in (219.20 mm)
Width	5 in (127.00 mm)
Depth	4.13 in (104.90 mm)

Environment

Certifications	CSA LR60905 class 3211 05 UL listed file E42243 CCN NLRV
Nema Enclosure Rating	NEMA 1 painted sheet steel

Ordering and shipping details

Category	21103-2510,2511,2512 M,T
Discount Schedule	CP1
Returnability	No

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	16.00 oz (453.592 g)

Contractual warranty

Warranty	18 months
----------	-----------