

# Product data sheet

Specifications



Manual starter, integral horsepower, NEMA M1, 600VAC, 3 pole, 10HP at 380/575VAC, 3 phase, no indicator, NEMA 7/9

2510MCR3

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 1,317.64 USD

## Main

Product	Manual Starter
Type	M
Nema Size	M-1

## Complementary

Control Unit	Push-button
Pilot Light	No indicator
Horsepower Rating	7.5 hp 200...230 V AC, 3 phase 10 hp 380...575 V AC, 3 phase
Voltage Rating	600 V AC
Number Of Poles	3P
Starter Type	Non reversing
Electrical Connection	Pressure wire clamp
Overload Relay Type	Melting alloy
Number Of Thermal Units Required	3
Wire Gauge	AWG 14...AWG 8 copper
Auxiliary Contacts	Without
Height	10.5 in (266.70 mm)
Width	6 in (152.40 mm)
Depth	6.13 in (155.70 mm)

## Environment

Certifications	UL listed file E58760 CCN NPXZ CSA LR26817 class 3218 04
Nema Enclosure Rating	NEMA 7/9 cast iron

## Ordering and shipping details

Category	US10CP121103
Discount Schedule	0CP1
Gtin	785901800620

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Returnability	Yes
Country Of Origin	MX

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.30 in (21.082 cm)
Package 1 Width	8.10 in (20.574 cm)
Package 1 Length	12.30 in (31.242 cm)
Package 1 Weight	31.00 lb(US) (14.061 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability




**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
 Pvc Free	
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>