

# Product data sheet

Specifications



## Manual Starter - NEMA 7&9 - 2P - Size M1 - 250VDC

2510MCR5

Discontinued on: Oct 12, 2021

Discontinued

### Main

Product	Manual Starter
Type	M
Nema Size	M-1

### Complementary

Control Unit	Push-button
Pilot Light	No indicator
Horsepower Rating	1.5 hp 115 V DC 2 hp 230 V DC
Voltage Rating	250 V DC
Number Of Poles	2P
Starter Type	Non reversing
Electrical Connection	Pressure wire clamp
Overload Relay Type	Melting alloy
Number Of Thermal Units Required	1
Wire Gauge	AWG 14...AWG 8 copper
Auxiliary Contacts	Without
Height	10.5 in (266.70 mm)
Width	6 in (152.40 mm)
Depth	6.13 in (155.70 mm)

### Environment

Certifications	UL listed file E58760 CCN NPXZ CSA LR26817 class 3218 04
Nema Enclosure Rating	NEMA 7/9 cast iron

### Ordering and shipping details

Category	21103-2510,2511,2512 M,T
Discount Schedule	CP1
Returnability	No

### Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

## Contractual warranty

Warranty	18 months
----------	-----------