

# 2512FS101P

## Two Speed Manual Starter- Flush Mounted - 1P- Toggle -Two Red Indicator - 277VAC

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\*\* : 494.90 USD



### Main

Product	Duplex Unit Manual Starter
Type	F
Overload Relay Type	Melting alloy

### Complementary

Current Rating	16 A
Cable entry	Without
Horsepower Rating	1 hp 115 V AC 1 hp 230 V AC 1 hp 277 V AC
Voltage Rating	277 V AC
Number of Poles	1P
Control Unit	Toggle switch
Number of Phases	1 phase
Pilot Light	Red indicator
Reset	Manual
Motor starter type	2 speed
Electrical connection	Screw clamp terminals
Wire Gauge	AWG 14...AWG 12 copper
Height	133.35 mm (5.25 in)
Width	133.35 mm (5.25 in)
Depth	92.20 mm (3.63 in)

### Environment

Product certifications	UL listed file E42243 CCN NLRV CE CSA LR25490 class 3211 05
------------------------	---

NEMA Enclosure Rating	Not rated (flush plate) stainless steel standard size
-----------------------	---

### Ordering and shipping details

Category	21101 - 2510,2511,2512 F
Discount Schedule	CP1
GTIN	00785901554837
Package weight(Lbs)	0.60 kg (1.33 lb(US))
Returnability	No
Country of origin	MX

### Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
EU RoHS Directive	Not compliant
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.

### Contractual warranty

Warranty	18 months
----------	-----------