

Product data sheet

Specifications



voltage release Compact MN - 24 V AC 50/60Hz

29404

⚠ Discontinued

Main

Range	ComPact
Range Of Product	NS100...250 DC NR100...250 NSJ400...600 NR400...630 NS125E NB400...600 NS400...630 DC NSF150...250 NS400...630 NR100...630 NS100...250
Device Short Name	MN
Product Or Component Type	Voltage release
Device Application	Control
Voltage Release Type	Undervoltage release
[Uc] Control Circuit Voltage	24 V AC 50/60 Hz
Range Compatibility	ComPact ComPact NS ComPact Compact NB ComPact Compact NR ComPact Compact NSF ComPact Compact NSJ

Complementary

Operating Threshold	0.35...0.7 Un opening 0.85 Un closing
Response Time	< 50 ms
Supply Holding Power	< 5 VA
Auxiliary Connection Terminal	screw terminal 0.00...0.00 in² (0...1.5 mm²)

Ordering and shipping details

Category	01103-H,J,COMPACT NS UL/IEC CIRCUIT BREAKER ACCESSORIES
Discount Schedule	DE2
Gtin	00785901110088
Returnability	No
Country Of Origin	FR

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------