

Product data sheet

Specifications



NEMA Motor Starter, Type S,
replacement coil, 347 VAC 60 Hz,
NEMA Size 00, 0 and 1 starters
and 8903SM lighting

3104140055

! Discontinued

! Discontinued on: Nov 11, 2020

! End-of-service on: Dec 31, 2020

Main

Product Or Component Type	Coil
Accessory / Separate Part Destination	Class 8502 type SA (series A)/SB/SC contactor Class 8536 type SA (series A)/SB/SC starter Class 8903 type SM lighting contactor

Complementary

[Ue] Rated Operational Voltage	347 V AC 60 Hz
Inrush Power In Va	245 VA
Average Consumption	27 VA
Height	2.15 in (54.7 mm)
Width	3.21 in (81.5 mm)
Depth	1.90 in (48.3 mm)

Ordering and shipping details

Category	18079-SPARE PARTS DISCOUNT CP10
Discount Schedule	CP10
Gtin	00785901292104
Returnability	No
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
-------------------	--------------------------------------------
