

# Product data sheet

Specifications



## Replacement coil, 550/600VAC 50/60Hz, NEMA size 00, 0, 1 and 30 Amp contactor

3104140062

⚠ Discontinued on: Jan 23, 2021

⚠ Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

|                                       |   |
|---------------------------------------|---|
| Product Or Component Type             | Coil  |
| Accessory / Separate Part Destination | Class 8502 type SA (series A)/SB/SC contactor<br>Class 8536 type SA (series A)/SB/SC starter<br>Class 8903 type SM lighting contactor |

### Complementary

|                                |                                  |
|--------------------------------|----------------------------------|
| Nema Size                      | 1<br>00<br>0                     |
| [Ue] Rated Operational Voltage | 600 V AC 60 Hz<br>550 V AC 50 Hz |
| Inrush Power In Va             | 232 VA<br>245 VA                 |
| Average Consumption            | 27 VA<br>26 VA                   |
| Height                         | 2.15 in (54.7 mm)                |
| Width                          | 3.21 in (81.5 mm)                |
| Depth                          | 1.90 in (48.3 mm)                |

### Ordering and shipping details

|                   |              |
|-------------------|--------------|
| Category          | US1CP1018079 |
| Discount Schedule | CP10         |
| Gtin              | 785901078029 |
| Returnability     | Yes          |
| Country Of Origin | MX           |

### Packing Units

|                              |                     |
|------------------------------|---------------------|
| Unit Type Of Package 1       | PCE                 |
| Number Of Units In Package 1 | 1                   |
| Package 1 Height             | 2.80 in (7.112 cm)  |
| Package 1 Width              | 3.40 in (8.636 cm)  |
| Package 1 Length             | 2.10 in (5.334 cm)  |
| Package 1 Weight             | 7.04 oz (199.581 g) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

|                           |   |
|---------------------------|---|
| Eu Rohs Directive         | Not applicable, out of EU RoHS legal scope  |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a> |