

Product data sheet

Specifications



NEMA Motor Starter, Type S, replacement coil, 208 VAC 60 Hz, 4-5 pole, NEMA size 2 starter and 8903SP lighting

3106340044

Discontinued

Discontinued on: Nov 20, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Or Component Type	Coil
Accessory / Separate Part Destination	Class 8502 type SD contactor Class 8903 type SP lighting contactor

Complementary

Nema Size	2
[Ue] Rated Operational Voltage	208 V AC 60 Hz
Inrush Power In Va	438 VA
Average Consumption	38 VA
Height	2.61 in (66.2 mm)
Width	3.98 in (101.1 mm)
Depth	2.43 in (61.7 mm)

Ordering and shipping details

Category	US10CP118061
Discount Schedule	0CP1
Gtin	785901107385
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.60 in (6.6 cm)
Package 1 Width	3.98 in (10.1 cm)
Package 1 Length	2.44 in (6.2 cm)
Package 1 Weight	10.88 oz (308.443 g)

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Not applicable, out of EU RoHS legal scope
